



FP4 Flocculator

Portable Jar Tester with 4 position, timer and lighting system



Practical and reliable solution for on-site Jar Test

Portable flocculator in 4 positions that allows standard conditions to be adopted for jar test.

- Choice of 20-40-50-100-200 rpm stirring speeds
- Precise speed from an electronically controlled DC gear motor
- 4 samples can be processed in parallel
- Designed to be used on-site for immediate results
- Strong resistance to chemical and mechanical corrosion



INSTRUMENT - CODE

FP4

100-240 V / 50-60 Hz

F105A0117

TECHNICAL DATA

	FP4
CONSTRUCTION MATERIAL	Epoxy painted metal structure
NUMBER OF SAMPLES	4 positions
STAINLESS STEEL STIRRING RODS	Adjustable in height by a selflocking chuck
MONOSELECTOR	Same speed for each rod
ELECTRONIC SPEED CONTROL	20 - 40 - 50 - 100 - 200 rpm
TIMER	from 0 to 30 minutes (or continuous)
POWER	6 W
DIMENSIONS (WXHXD)	250x320x250 mm (9.8x12.6x9.8 in)
WEIGHT	4,8 Kg (10.6 lb)



We reserve the right to make technical alterations
We do not assume liability for errors in printing, typing or transmission

VELP Official Partner

DESIGNED AND MANUFACTURED IN ITALY



ITALY - HQ
Via Stazione 16
20865 Usmate (MB) Italy
Tel. +39 039 628811
velpitalia@velp.com

INDIA
velpindia@velp.com

USA
155 Keyland Court, Bohemia
NY 11716 - U.S.
Tel. +1 631 573 6002
velpusa@velp.com

CHINA
Xinlong Rd Building 28, Lane 1333
Shanghai city - China
Tel. +86 18017557329
velpchina@velp.com